



120 X 240 - 24  
120 X 240 Primary Volts - 24 Secondary Volts - 1Ø  
Industrial Control Transformer - Encapsulated

1053



Catalog #: AE010500

#### PRODUCT FEATURES

- UL and cUL listed
- Constructed out of electrical lamination with precision wound coils
- Fully encapsulated core and coil
- Available Fuse Kits and Accessories
- Covered under Acme's 10 year limited warranty

#### BENEFITS

- Molded terminal blocks with isolation barriers
- Dual labeling for easy product identification
- Heavy gauge steel mounting feet
- Fast wire connection terminal

#### UL STANDARD

UL 506

#### CSA STANDARD

C22.2 No 66

#### WARRANTY

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

#### GENERAL PRODUCT INFORMATION

VA:	500
Primary Voltage:	120 X 240
Secondary Voltage:	24
Frequency:	50/60 Hz
Max Temperature Rise:	55°C
UL Insulation Class:	105°C

#### PRODUCT MEASUREMENTS

Height (In./cm):	4.66 (11.8)
Width (In./cm):	5.25 (13.3)
Depth (In./cm):	5.53 (14.0)

#### CONFIGURATION

Mounting Type:	Floor
Wiring Diagram:	AE01

#### PACKAGING

Ship Weight (Lbs/Kg):	19.00 (8.6)
-----------------------	-------------

**COMPLIANCES**

UL Standard: UL 506  
UL Listed: File E79947  
CSA Standard: C22.2 No 66  
CSA Listed: LR7357-16  
Warranty: Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)