



220 X 440 - 110/115/120  
220 X 440 Primary Volts - 110/115/120 Secondary Volts - 1Ø  
Industrial Control Transformer - Encapsulated

1058



Catalog #: AE060050

#### PRODUCT FEATURES

- UL and cUL listed
- Constructed out of electrical lamination with precision wound coils
- Fully encapsulated core and coil
- Available Fuse Kits and Accessories
- Covered under Acme's 10 year limited warranty

#### BENEFITS

- Molded terminal blocks with isolation barriers
- Dual labeling for easy product identification
- Heavy gauge steel mounting feet
- Fast wire connection terminal

#### UL STANDARD

UL 506

#### CSA STANDARD

C22.2 No 66

#### WARRANTY

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

#### GENERAL PRODUCT INFORMATION

VA:	50
Primary Voltage:	220 X 440
Secondary Voltage:	110/115/120
Frequency:	50/60 Hz
Max Temperature Rise:	55°C
UL Insulation Class:	105°C

#### PRODUCT MEASUREMENTS

Height (In./cm):	2.81 (7.1)
Width (In./cm):	3.00 (7.6)
Depth (In./cm):	2.69 (6.8)

#### CONFIGURATION

Mounting Type:	Floor
Wiring Diagram:	AE06

#### PACKAGING

Ship Weight (Lbs/Kg):	2.5 (1.1)
-----------------------	-----------

**COMPLIANCES**

UL Standard: UL 506  
UL Listed: File E79947  
CSA Standard: C22.2 No 66  
CSA Listed: LR7357-16  
Warranty: Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)