



200/220/440 - 23/110  
200/220/440 Primary Volts - 23/110 Secondary Volts - 1Ø - CE Marked  
Industrial Control Transformer - Encapsulated

1054



Catalog #: CE020150

**PRODUCT FEATURES**

- UL and cUL listed
- UL and cUL listed, CE Marked
- CE Marked
- Constructed out of electrical lamination with precision wound coils
- Constructed out of electrical lamination with precision wound coils
- Fully encapsulated core and coil
- Available Fuse Kits and Accessories
- Covered under Acme's 10 year limited warranty

**BENEFITS**

- Molded terminal blocks with isolation barriers
- Dual labeling for easy product identification
- Heavy gauge steel mounting feet
- Fast wire connection terminal

**UL STANDARD**

UL 506

**CSA STANDARD**

C22.2 No 66

**WARRANTY**

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

**GENERAL PRODUCT INFORMATION**

VA:	150
Primary Voltage:	200/220/440
Secondary Voltage:	23/110
Frequency:	50/60 Hz
Max Temperature Rise:	55°C
UL Insulation Class:	105°C

**PRODUCT MEASUREMENTS**

Height (In./cm):	3.41 (8.6)
Width (In./cm):	4.50 (11.4)
Depth (In./cm):	4.03 (10.2)

**CONFIGURATION**

Mounting Type:	Floor
Wiring Diagram:	CE02

**PACKAGING**

Ship Weight (Lbs/Kg): 6.8 (3.1)

**COMPLIANCES**

UL Standard: UL 506  
UL Listed: File E79947  
CSA Standard: C22.2 No 66  
CSA Listed: LR7357-16  
CE: CE Marked  
Warranty: Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)