



200/220/440 - 23/110  
200/220/440 Primary Volts - 23/110 Secondary Volts - 1Ø - CE Marked  
Industrial Control Transformer - Encapsulated

1054



Catalog #: CE020350

#### PRODUCT FEATURES

- UL and cUL listed
- UL and cUL listed, CE Marked
- CE Marked
- Constructed out of electrical lamination with precision wound coils
- Constructed out of electrical lamination with precision wound coils
- Fully encapsulated core and coil
- Available Fuse Kits and Accessories
- Covered under Acme's 10 year limited warranty

#### BENEFITS

- Molded terminal blocks with isolation barriers
- Dual labeling for easy product identification
- Heavy gauge steel mounting feet
- Fast wire connection terminal

#### UL STANDARD

UL 506

#### CSA STANDARD

C22.2 No 66

#### WARRANTY

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

#### GENERAL PRODUCT INFORMATION

VA: 350  
Primary Voltage: 200/220/440  
Secondary Voltage: 23/110  
Frequency: 50/60 Hz  
Max Temperature Rise: 55°C  
UL Insulation Class: 105°C

#### PRODUCT MEASUREMENTS

Height (In./cm): 4.03 (10.2)  
Width (In./cm): 5.25 (13.3)  
Depth (In./cm): 5.53 (14.0)

#### CONFIGURATION

Mounting Type: Floor  
Wiring Diagram: CE02

#### PACKAGING

Ship Weight (Lbs/Kg): 13.5 (6.1)

**COMPLIANCES**

UL Standard: UL 506  
UL Listed: File E79947  
CSA Standard: C22.2 No 66  
CSA Listed: LR7357-16  
CE: CE Marked  
Warranty: Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)