



240 X 480 - 24  
240 X 480 Primary Volts - 24 Secondary Volts - 1Ø - CE Marked  
Industrial Control Transformer - Encapsulated

1063



Catalog #: CE030050

**PRODUCT FEATURES**

- UL and cUL listed
- CE Marked
- Constructed out of electrical lamination with precision wound coils
- Fully encapsulated core and coil
- Available Fuse Kits and Accessories
- Covered under Acme's 10 year limited warranty

**BENEFITS**

- Molded terminal blocks with isolation barriers
- Dual labeling for easy product identification
- Heavy gauge steel mounting feet
- Fast wire connection terminal

**UL STANDARD**

UL 506

**CSA STANDARD**

C22.2 No 66

**WARRANTY**

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

**GENERAL PRODUCT INFORMATION**

VA:	50
Primary Voltage:	240 X 480
Secondary Voltage:	24
Frequency:	50/60 Hz
Max Temperature Rise:	55°C
UL Insulation Class:	105°C

**PRODUCT MEASUREMENTS**

Height (In./cm):	2.81 (7.1)
Width (In./cm):	3.00 (7.6)
Depth (In./cm):	3.00 (7.6)

**CONFIGURATION**

Mounting Type:	Floor
Wiring Diagram:	CE03

**PACKAGING**

Ship Weight (Lbs/Kg):	2.5 (1.1)
-----------------------	-----------

**COMPLIANCES**

UL Standard: UL 506  
UL Listed: File E79947  
CSA Standard: C22.2 No 66  
CSA Listed: LR7357-16  
CE: CE Marked  
Warranty: Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)