



380/400/415 - 110/220  
380/400/415 Primary Volts - 110/220 Secondary Volts - 1Ø - CE Marked  
Industrial Control Transformer - Encapsulated

1067



Catalog #: CE040100

#### PRODUCT FEATURES

- UL and cUL listed, CE Marked
- Constructed out of electrical lamination with precision wound coils
- Fully encapsulated core and coil
- Available Fuse Kits and Accessories
- Covered under Acme's 10 year limited warranty

#### BENEFITS

- Molded terminal blocks with isolation barriers
- Dual labeling for easy product identification
- Heavy gauge steel mounting feet
- Fast wire connection terminal

#### UL STANDARD

UL 506

#### CSA STANDARD

C22.2 No 66

#### WARRANTY

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

#### GENERAL PRODUCT INFORMATION

VA:	100
Primary Voltage:	380/400/415
Secondary Voltage:	110/220
Frequency:	50/60 Hz
Max Temperature Rise:	55°C
UL Insulation Class:	105°C

#### PRODUCT MEASUREMENTS

Height (In./cm):	3.22 (8.1)
Width (In./cm):	3.75 (9.5)
Depth (In./cm):	3.53 (8.9)

#### CONFIGURATION

Mounting Type:	Floor
Wiring Diagram:	CE04

#### PACKAGING

Ship Weight (Lbs/Kg):	4.3 (1.9)
-----------------------	-----------

**COMPLIANCES**

UL Standard: UL 506  
UL Listed: File E79947  
CSA Standard: C22.2 No 66  
CSA Listed: LR7357-16  
CE: CE Marked  
Warranty: Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)