



230Δ - 230Y/133
230Δ Primary Volts - 230Y/133 Secondary Volts - 3Ø
Drive Isolation Transformer - Three Phase

1027



Catalog #: DTFA0514S

PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R with optional Weather Shield
- Aluminum foil windings
- Copper bus bar terminations
- Wound/Distributed core construction
- Covered under Acme's 10 year limited warranty
- Optional Thermal Switch - part # PL79900
- Optional wall mounting kit - part # PL79912

BENEFITS

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units

UL STANDARD

UL 1561

CSA STANDARD

C22.2 No. 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

KVA:	51.00
Primary Voltage:	230Δ
Secondary Voltage:	230Y/133
Frequency:	60 Hz
ANFC Taps:	2
BNFC Taps:	2
Taps % Steps:	2.5%
Max Temperature Rise:	150°C
UL Insulation Class:	220°C

PRODUCT MEASUREMENTS

Height (In./cm):	29.9 (75.9)
Width (In./cm):	28.15 (71.5)
Depth (In./cm):	22.37 (56.8)

CONFIGURATION

Construction Type:	Ventilated
--------------------	------------

Mounting Type: Floor
Weather Shield: WSA2
Wiring Diagram: 59

PACKAGING

Ship Weight (Lbs/Kg): 375 (170.0)

COMPLIANCES

UL Standard: UL 1561
UL Listed: File E12547
CSA Standard: C22.2 No. 47
CSA Listed: LR7357-32
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf