



230Δ - 230Y/133  
230Δ Primary Volts - 230Y/133 Secondary Volts - 3Ø  
Drive Isolation Transformer - Three Phase

1027



Catalog #: DTFA0754S

**PRODUCT FEATURES**

- UL listed, CSA certified
- UL Type 3R with optional Weather Shield
- Aluminum foil windings
- Copper bus bar terminations
- Wound/Distributed core construction
- Covered under Acme's 10 year limited warranty
- Optional Thermal Switch - part # PL79900
- Optional wall mounting kit - part # PL79912

**BENEFITS**

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units

**UL STANDARD**

UL 1561

**CSA STANDARD**

C22.2 No. 47

**WARRANTY**

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

**GENERAL PRODUCT INFORMATION**

KVA:	75.00
Primary Voltage:	230Δ
Secondary Voltage:	230Y/133
Frequency:	60 Hz
ANFC Taps:	2
BNFC Taps:	2
Taps % Steps:	2.5%
Max Temperature Rise:	150°C
UL Insulation Class:	220°C

**PRODUCT MEASUREMENTS**

Height (In./cm):	29.9 (75.9)
Width (In./cm):	28.15 (71.5)
Depth (In./cm):	22.37 (56.8)

**CONFIGURATION**

Construction Type: Ventilated

Mounting Type: Floor  
Weather Shield: WSA2  
Wiring Diagram: 59

**PACKAGING**

Ship Weight (Lbs/Kg): 525 (238.0)

**COMPLIANCES**

UL Standard: UL 1561  
UL Listed: File E12547  
CSA Standard: C22.2 No. 47  
CSA Listed: LR7357-32  
Warranty: Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)