



208/500 - 85/100/110
208/500 Primary Volts - 85/100/110 Secondary Volts - 1Ø
Industrial Control Transformer - Finger/Guard

1069



Catalog #: FS32000

PRODUCT FEATURES

- UL listed, CSA certified, and CE Marked
- Voltage Regulation exceeds NEMA requirements
- Constructed out of electrical lamination with precision wound coils
- Touch Protected terminations
- Covered under Acme's 10 year limited warranty

BENEFITS

- Small and lightweight design
- Durable molded plastic terminals
- Fast wire connection terminal

UL STANDARD

UL 506

CSA STANDARD

C22.2 No 66

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

VA:	2000
Primary Voltage:	208/500
Secondary Voltage:	85/100/110
Frequency:	50/60 Hz
Max Temperature Rise:	80°C
UL Insulation Class:	130°C

PRODUCT MEASUREMENTS

Height (In./cm):	7.70 (19.6)
Width (In./cm):	7.50 (19.1)
Depth (In./cm):	7.76 (19.7)

CONFIGURATION

Mounting Type:	Floor
Wiring Diagram:	C

PACKAGING

Ship Weight (Lbs/Kg):	66 (29.9)
-----------------------	-----------

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No 66
CSA Listed: LR7357-16
CE: CE Marked
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf