



480 - 120/240  
Snap In Breakers - 304 Stainless Steel - 480 Primary Volts - 120/240 Secondary Volts - 1Ø  
Panel Tran Zone Power Centers - Single Phase

1086



Catalog #: PT061150007SS

**PRODUCT FEATURES**

- Meets or exceeds UL, CSA, NEMA, ANSI, and OSHA standards
- Snap-in Breakers
- UL Type 3R Enclosure 304 Stainless Steel
- Shielded for cleaner power
- Covered under Acme's 10 year limited warranty

**BENEFITS**

- Fully compliant with NEC 450-3
- Designed for indoor and outdoor applications
- Electrostatic shield for enhanced protection
- Primary and Secondary main circuit breakers provided

**UL STANDARD**

UL 1062

**CSA STANDARD**

C22.2 No 47

**WARRANTY**

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

**GENERAL PRODUCT INFORMATION**

kVA:	7.50
Primary Voltage:	480
Secondary Voltage:	120/240
Frequency:	60 Hz
ANFC Taps:	-
BNFC Taps:	2
Taps % Steps:	5%
Max Temperature Rise:	115°C
UL Insulation Class:	180°C
Primary Breaker:	ED42B025L (25A)
Secondary Breaker:	Q240 (40A)

**PRODUCT MEASUREMENTS**

Height (In./cm):	32.13 (81.6)
Width (In./cm):	15.88 (40.3)
Depth (In./cm):	11 (27.9)

**CONFIGURATION**

Construction Type:	Encapsulated
Mounting Type:	Wall

**PACKAGING**

Ship Weight (Lbs/Kg): 160 (72.6)

**COMPLIANCES**

UL Standard: UL 1062  
UL Listed: File E56936  
CSA Standard: C22.2 No 47  
CSA Listed: LR7357-39  
Warranty: Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)