



480 - 120/240
Snap In Breakers - 304 Stainless Steel - 480 Primary Volts - 120/240 Secondary Volts - 1Ø
Panel Tran Zone Power Centers - Single Phase

1086



Catalog #: PT061150015SS

PRODUCT FEATURES

- Meets or exceeds UL, CSA, NEMA, ANSI, and OSHA standards
- Snap-in Breakers
- UL Type 3R Enclosure 304 Stainless Steel
- Shielded for cleaner power
- Covered under Acme's 10 year limited warranty

BENEFITS

- Fully compliant with NEC 450-3
- Designed for indoor and outdoor applications
- Electrostatic shield for enhanced protection
- Primary and Secondary main circuit breakers provided

UL STANDARD

UL 1062

CSA STANDARD

C22.2 No 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

kVA:	15.00
Primary Voltage:	480
Secondary Voltage:	120/240
Frequency:	60 Hz
ANFC Taps:	-
BNFC Taps:	2
Taps % Steps:	5%
Max Temperature Rise:	115°C
UL Insulation Class:	180°C
Primary Breaker:	ED42B050L (50A)
Secondary Breaker:	Q270 (70A)

PRODUCT MEASUREMENTS

Height (In./cm):	34.38 (87.3)
Width (In./cm):	17.13 (43.5)
Depth (In./cm):	12.38 (31.4)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall

PACKAGING

Ship Weight (Lbs/Kg): 240 (109)

COMPLIANCES

UL Standard: UL 1062
UL Listed: File E56936
CSA Standard: C22.2 No 47
CSA Listed: LR7357-39
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf