



240 X 480 - 24/48
240 X 480 Primary Volts - 24/48 Secondary Volts - 1Ø
Buck-Boost Transformer - Single Phase

1084



Catalog #: T137920

PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R epoxy encapsulated
- Single or Three Phase Applications
- Wall Mounted
- Covered under Acme's 10 year limited warranty

BENEFITS

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in KVA

UL STANDARD

UL 506

CSA STANDARD

C22.2 No 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

VA:	-
kVA:	1.00
Primary Voltage:	240 X 480
Secondary Voltage:	24/48
Frequency:	60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

PRODUCT MEASUREMENTS

Height (In./cm):	10.50 (26.7)
Width (In./cm):	5.50 (14.0)
Depth (In./cm):	5.13 (13.0)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall

PACKAGING

Ship Weight (Lbs/Kg):	24 (10.9)
-----------------------	-----------

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No 47
CSA Listed: LR7357-32
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf