



480Δ - 208Y/120
480Δ Primary Volts - 208Y/120 Secondary Volts - 3Ø
Dry Type Distribution Transformer - Three Phase

1017



Catalog #: T2A533091S

PRODUCT FEATURES

- UL listed, CSA certified
- Fully encapsulated core and coil
- Meet CSA C802.2 Efficiency
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

UL STANDARD

UL 506

CSA STANDARD

C22.2 No. 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

KVA:	6.00
Primary Voltage:	480Δ
Secondary Voltage:	208Y/120
Frequency:	60 Hz
ANFC Taps:	-
BNFC Taps:	2
Taps % Steps:	5.0%
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

PRODUCT MEASUREMENTS

Height (In./cm):	11.83 (30.0)
Width (In./cm):	14.17 (36.0)
Depth (In./cm):	8.82 (22.4)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall
Knockouts (In./Cm):	0.75-1.25 (1.9-3.2)

Wiring Diagram: 21

PACKAGING

Ship Weight (Lbs/Kg): 140 (63.5)

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No. 47
CSA Listed: LR7357-32
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf