



600 - 120/240
600 Primary Volts - 120/240 Secondary Volts - Three Windings - 1Ø
Dry Type Distribution Transformer - Single Phase

1009



Catalog #: T153106

PRODUCT FEATURES

- UL listed, CSA certified
- Fully encapsulated core and coil
- Meet CSA C802.2 Efficiency
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

BENEFITS

Quiet operation with sound levels below NEMA standards

UL STANDARD

UL 506

CSA STANDARD

C22.2 No. 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

kVA:	0.15
Primary Voltage:	600
Secondary Voltage:	120/240
Frequency:	50/60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	130°C

PRODUCT MEASUREMENTS

Height (In./cm):	7.16 (18.2)
Width (In./cm):	3.89 (9.9)
Depth (In./cm):	3.67 (9.3)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall
Knockouts (In./Cm):	0.875 (2.2)
Wiring Diagram:	8

PACKAGING

Ship Weight (Lbs/Kg):	7 (3.2)
-----------------------	---------

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No. 47
CSA Listed: LR7357-26
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf