



240/480/600 - 100/120
240/480/600 Primary Volts - 100/120 Secondary Volts - 1Ø
Industrial Control Transformer - Harsh Environment

1077



Catalog #: T153929

PRODUCT FEATURES

UL listed, CSA certified
UL Type 3R epoxy encapsulated
Fully encapsulated core and coil
Wall Mounted
Voltage Regulation exceeds NEMA requirements
Covered under Acme's 10 year limited warranty

BENEFITS

Designed for outside control panel installation

UL STANDARD

UL 506

CSA STANDARD

C22.2 No 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

VA: 2000
Primary Voltage: 240/480/600
Secondary Voltage: 100/120
Frequency: 50/60 Hz
Max Temperature Rise: 55°C
UL Insulation Class: 155°C

PRODUCT MEASUREMENTS

Height (In./cm): 14.77 (37.5)
Width (In./cm): 10.31 (26.2)
Depth (In./cm): 7.13 (18.1)

CONFIGURATION

Construction Type: Encapsulated
Mounting Type: Wall
Wiring Diagram: C

PACKAGING

Ship Weight (Lbs/Kg): 80 (36.3)

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No 47
CSA Listed: LR7357-32
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf