



95-132 X 166-228 X 192-264 X 384-528 - 120/208/240
95-132 X 166-228 X 192-264 X 384-528 Primary Volts - 120/208/240 Secondary Volts - 1Ø
Power Conditioning - Hardwired Models

1089



Catalog #: T169437

PRODUCT FEATURES

- Input range of +10/-20%
- Effective noise rejection
- UL Listed and CSA Certified
- Encapsulated transformer
- Covered under Acme's 10 year limited warranty

BENEFITS

- Suppressing transient spikes and surges
- Rapid response to line and load changes
- Inherent overload and short circuit protection

UL STANDARD

UL 1012

CSA STANDARD

C22.2 No. 66

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

kVA:	5.00
Primary Voltage:	95-132 X 166-228 X 192-264 X 384-528
Secondary Voltage:	120/208/240
Frequency:	60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

PRODUCT MEASUREMENTS

Height (In./cm):	22 (55.9)
Width (In./cm):	12.54 (31.9)
Depth (In./cm):	12.2 (31)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Floor/Wall
Wiring Diagram:	16

PACKAGING

Ship Weight (Lbs/Kg):	295 (134)
-----------------------	-----------

COMPLIANCES

UL Standard: UL 1012
UL Listed: File E86492
CSA Standard: C22.2 No. 66
CSA Listed: LR7357-33
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf