



120 - 12
120 Primary Volts - 12 Secondary Volts - 1Ø
Low Voltage Lighting Transformer - Single Phase

1078



Catalog #: T179621S

PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 2 Enclosures
- Fully encapsulated core and coil
- Wall Mounted
- Black Finish UL Type 2 Enclosure
- Input Auto-Thermal reset switch
- Output circuit breaker
- Covered under Acme's 10 year limited warranty

BENEFITS

- Copper lead wires for hardwiring
- Primary and secondary overload protection
- Full fault current carrying Farady Shield
- Single and dual knockouts

UL STANDARD

UL 506

CSA STANDARD

C22.2 No 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

VA: 300
Primary Voltage: 120
Secondary Voltage: 12
Frequency: 60 Hz
Max Temperature Rise: 115°C
UL Insulation Class: 180°C

PRODUCT MEASUREMENTS

Height (In./cm): 11.68 (29.7)
Width (In./cm): 4.66 (11.8)
Depth (In./cm): 4.57 (11.6)

CONFIGURATION

Construction Type: Encapsulated
Mounting Type: Wall
Knockouts (In./Cm): Two 0.875 (2.2) signal knockouts on each side
Knockouts 2 (In./Cm): Two dual 0.875 (2.2) and 1.125 (2.9) knockouts on bottom cover

Wiring Diagram: V
CB Rating: 40 Amp
CB Style: Push To Reset Thermal Breaker

PACKAGING

Ship Weight (Lbs/Kg): 11 (5.0)

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No 47
CSA Listed: LR7357-32
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf