



240 X 480 - 24/48  
240 X 480 Primary Volts - 24/48 Secondary Volts - 1Ø  
Buck-Boost Transformer - Single Phase

1084



Catalog #: T181062

#### PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R epoxy encapsulated
- Single or Three Phase Applications
- Wall Mounted
- Covered under Acme's 10 year limited warranty

#### BENEFITS

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in KVA

#### UL STANDARD

UL 506

#### CSA STANDARD

C22.2 No 47

#### WARRANTY

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

#### GENERAL PRODUCT INFORMATION

VA:	100
kVA:	-
Primary Voltage:	240 X 480
Secondary Voltage:	24/48
Frequency:	50/60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

#### PRODUCT MEASUREMENTS

Height (In./cm):	7.16 (18.2)
Width (In./cm):	3.89 (9.9)
Depth (In./cm):	3.67 (9.3)

#### CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall

#### PACKAGING

Ship Weight (Lbs/Kg):	5 (2.3)
-----------------------	---------

**COMPLIANCES**

UL Standard: UL 506  
UL Listed: File E79947  
CSA Standard: C22.2 No 47  
CSA Listed: LR7357-26  
Warranty: Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)