



240 X 480 - 120
240 X 480 Primary Volts - 120 Secondary Volts - 1Ø
Industrial Control Transformer - Harsh Environment

1076



Catalog #: T181217

PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R epoxy encapsulated
- Fully encapsulated core and coil
- Wall Mounted
- Voltage Regulation exceeds NEMA requirements
- Covered under Acme's 10 year limited warranty

BENEFITS

- Designed for outside control panel installation

UL STANDARD

- UL 506

CSA STANDARD

- C22.2 No 47

WARRANTY

- Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

- VA: 1000
- Primary Voltage: 240 X 480
- Secondary Voltage: 120
- Frequency: 50/60 Hz
- Max Temperature Rise: 55°C
- UL Insulation Class: 155°C

PRODUCT MEASUREMENTS

- Height (In./cm): 13.10 (33.3)
- Width (In./cm): 10.31 (26.2)
- Depth (In./cm): 7.13 (18.1)

CONFIGURATION

- Construction Type: Encapsulated
- Mounting Type: Wall
- Wiring Diagram: B

PACKAGING

- Ship Weight (Lbs/Kg): 55 (24.9)

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No 47
CSA Listed: LR7357-32
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf