



240 - 120/240  
Autotransformer - 240 Primary Volts - 120/240 Secondary Volts - 1Ø  
Dry Type Distribution Transformer - Single Phase

1006



Catalog #: T253064

**PRODUCT FEATURES**

- UL listed, CSA certified
- Fully encapsulated core and coil
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

**BENEFITS**

Quiet operation with sound levels below NEMA standards

**UL STANDARD**

UL 506

**CSA STANDARD**

C22.2 No. 47

**WARRANTY**

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

**GENERAL PRODUCT INFORMATION**

kVA:	5.00
Primary Voltage:	240
Secondary Voltage:	120/240
Frequency:	60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

**PRODUCT MEASUREMENTS**

Height (In./cm):	13.00 (33.0)
Width (In./cm):	5.50 (14.0)
Depth (In./cm):	5.13 (13.0)

**CONFIGURATION**

Construction Type:	Encapsulated
Mounting Type:	Wall
Knockouts (In./Cm):	5.50 (14.0)
Weather Shield:	WSA3
Wiring Diagram:	12

**PACKAGING**

Ship Weight (Lbs/Kg):	38 (17.2)
-----------------------	-----------

**COMPLIANCES**

UL Standard: UL 506  
UL Listed: File E79947  
CSA Standard: C22.2 No. 47  
CSA Listed: LR7357-32  
Warranty: Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)