



240X480 - 120/240
316 Stainless Steel - 240 X 480 Primary Volts - 120/240 Secondary Volts - Four Windings - 1Ø
Dry Type Distribution Transformer - Single Phase

1007



Catalog #: T253517SS

PRODUCT FEATURES

- UL listed, CSA certified
- Fully encapsulated core and coil
- Meet CSA C802.2 Efficiency
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

UL STANDARD

UL 506

CSA STANDARD

C22.2 No. 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

KVA:	15.00
Primary Voltage:	240 X 480
Secondary Voltage:	120/240
Frequency:	60 Hz
ANFC Taps:	2
BNFC Taps:	4
Taps % Steps:	2.5%
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

PRODUCT MEASUREMENTS

Height (In./cm):	16.94 (43.0)
Width (In./cm):	14.12 (35.9)
Depth (In./cm):	11.59 (29.4)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall
Wiring Diagram:	4

PACKAGING

Ship Weight (Lbs/Kg): 170 (77.1)

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No. 47
CSA Listed: LR7357-32
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf