



120/208/240/277 - 120/240
120/208/240/277 Primary Volts - 120/240 Secondary Volts - 1Ø
Dry Type Distribution Transformer - Single Phase

1001



Catalog #: T279744S

PRODUCT FEATURES

- UL listed, CSA certified
- Fully encapsulated core and coil
- Meet CSA C802.2 Efficiency
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

UL STANDARD

UL 506

CSA STANDARD

C22.2 No. 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

| | |
|-----------------------|-----------------|
| kVA: | 5.00 |
| Primary Voltage: | 120/208/240/277 |
| Secondary Voltage: | 120/240 |
| Frequency: | 60 Hz |
| Max Temperature Rise: | 115°C |
| UL Insulation Class: | 180°C |

PRODUCT MEASUREMENTS

| | |
|------------------|--------------|
| Height (In./cm): | 14.38 (36.5) |
| Width (In./cm): | 10.31 (26.2) |
| Depth (In./cm): | 7.13 (18.1) |

CONFIGURATION

| | |
|---------------------|---------------------|
| Construction Type: | Encapsulated |
| Mounting Type: | Wall |
| Knockouts (In./Cm): | 0.75-1.25 (1.9-3.2) |
| Wiring Diagram: | 23 |

PACKAGING

Ship Weight (Lbs/Kg): 75 (34.0)

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No. 47
CSA Listed: LR7357-32
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf