



208Δ - 208Y/120  
208Δ Primary Volts - 208Y/120 Secondary Volts - 3Ø  
Dry Type Distribution Transformer - Three Phase

1011



Catalog #: T2A792701S

**PRODUCT FEATURES**

- UL listed, CSA certified
- Fully encapsulated core and coil
- Meet CSA C802.2 Efficiency
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

**BENEFITS**

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

**UL STANDARD**

UL 506

**CSA STANDARD**

C22.2 No. 47

**WARRANTY**

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

**GENERAL PRODUCT INFORMATION**

KVA:	9.00
Primary Voltage:	208Δ
Secondary Voltage:	208Y/120
Frequency:	60 Hz
ANFC Taps:	-
BNFC Taps:	2
Taps % Steps:	5.0%
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

**PRODUCT MEASUREMENTS**

Height (In./cm):	14.03 (36.0)
Width (In./cm):	17.77 (45.1)
Depth (In./cm):	11.52 (29.3)

**CONFIGURATION**

Construction Type:	Encapsulated
Mounting Type:	Wall
Knockouts (In./Cm):	0.75-1.25 (1.9-3.2)

Wiring Diagram: 60

**PACKAGING**

Ship Weight (Lbs/Kg): 180 (81.6)

**COMPLIANCES**

UL Standard: UL 506  
UL Listed: File E79947  
CSA Standard: C22.2 No. 47  
CSA Listed: LR7357-32  
Warranty: Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)