



380Δ - 220Y/127  
380Δ Primary Volts - 220Y/127 Secondary Volts - 3Ø  
Dry Type Distribution Transformer - Three Phase

1015



Catalog #: T2A795543S

#### PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R with optional Weather Shield
- Floor Mounted
- Ground Studs for use with non-metallic conduit
- Aluminum Bus termination
- Covered under Acme's 10 year limited warranty

#### BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

#### UL STANDARD

UL 1561

#### CSA STANDARD

C22.2 No. 47

#### WARRANTY

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

#### GENERAL PRODUCT INFORMATION

kVA:	75.00
Primary Voltage:	380Δ
Secondary Voltage:	220Y/127
Frequency:	50 Hz
ANFC Taps:	2
BNFC Taps:	4
Taps % Steps:	2.5%
Max Temperature Rise:	150°C
UL Insulation Class:	220°C

#### PRODUCT MEASUREMENTS

Height (In./cm):	35.47 (90.1)
Width (In./cm):	31.90 (80.0)
Depth (In./cm):	26.88 (68.3)

#### CONFIGURATION

Construction Type:	Ventilated
Mounting Type:	Floor
Weather Shield:	WSA3
Wiring Diagram:	20

**PACKAGING**

Ship Weight (Lbs/Kg): 693 (314.3)

**COMPLIANCES**

UL Standard: UL 1561  
UL Listed: File E12547  
CSA Standard: C22.2 No. 47  
CSA Listed: LR7357-32  
Warranty: Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)