



240Δ - 208Y/120
240Δ Primary Volts - 208Y/120 Secondary Volts - 3Ø
Dry Type Distribution Transformer - Three Phase

1013



Catalog #: T3030K0044B

PRODUCT FEATURES

- UL listed, CSA certified
- Meet DOE 2016 efficiency requirements
- UL Type 3R with Weather Shield
- Floor Mounted
- Ground Studs for use with non-metallic conduit
- Aluminum Bus termination
- Covered under Acme's 10 year limited warranty

BENEFITS

Quiet operation with sound levels below NEMA standards

DOE

Meets or exceed U.S. DOE 10 CFR Part 431

UL STANDARD

UL 1561

CSA STANDARD

C22.2 No. 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

| | |
|-----------------------|----------|
| kVA: | 30.00 |
| Primary Voltage: | 240Δ |
| Secondary Voltage: | 208Y/120 |
| Frequency: | 60 Hz |
| ANFC Taps: | 2 |
| BNFC Taps: | 2 |
| Taps % Steps: | 2.5% |
| Max Temperature Rise: | 150°C |
| UL Insulation Class: | 220°C |

PRODUCT MEASUREMENTS

| | |
|------------------|--------------|
| Height (In./cm): | 25.50 (64.8) |
| Width (In./cm): | 24.39 (61.9) |
| Depth (In./cm): | 19.37 (49.2) |

CONFIGURATION

Construction Type: Ventilated

Mounting Type: Floor
Wiring Diagram: 19

PACKAGING

Ship Weight (Lbs/Kg): 365 (166.0)

COMPLIANCES

DOE: Meets or exceed U.S. DOE 10 CFR Part 431
UL Standard: UL 1561
UL Listed: File E12547
CSA Standard: C22.2 No. 47
CSA Listed: LR7357-32
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf