



190/200/208/220/240Δ - 400Y/231
190/200/208/220/240Δ Primary Volts - 400Y/231 Secondary Volts - 3Ø
Dry Type Distribution Transformer - Three Phase

1010



Catalog #: T3030K0170BS

PRODUCT FEATURES

- UL listed, CSA certified
- Meet DOE 2016 efficiency requirements
- UL Type 3R with Weather Shield
- Floor Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

DOE

- Meets or exceed U.S. DOE 10 CFR Part 431

UL STANDARD

- UL 1561

CSA STANDARD

- C22.2 No. 47

WARRANTY

- Acme Electric Warranty Card
- www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

kVA:	30.00
Primary Voltage:	190/200/208/220/240Δ
Secondary Voltage:	400Y/231
Frequency:	60 Hz
Max Temperature Rise:	150°C
UL Insulation Class:	220°C

PRODUCT MEASUREMENTS

Height (In./cm):	25.50 (64.8)
Width (In./cm):	24.39 (62.0)
Depth (In./cm):	19.37 (49.2)

CONFIGURATION

Construction Type:	Ventilated
Mounting Type:	Floor
Wiring Diagram:	74

PACKAGING

Ship Weight (Lbs/Kg): 360 (163.2)

COMPLIANCES

DOE: Meets or exceed U.S. DOE 10 CFR Part 431

UL Standard: UL 1561

UL Listed: File E12547

CSA Standard: C22.2 No. 47

CSA Listed: LR7357-32

Warranty: Acme Electric Warranty Card

www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf