



480 DELTA PRIMARY VOLTS — 240 DELTA/120 TAP SECONDARY VOLTS — MAY BE USED ON A 4 WIRE 480Y/277 VOLTS SUPPLY— 3Ø, 60 Hz

kVA	Catalog Number	Height (Inches)(Cm.)	Width (Inches)(Cm.)	Depth (Inches)(Cm.)	Weight (Lbs.)(Kg.)	Mounting Type (Wall)(Floor)	Knockouts (Inches)(Cm.)	Optional Electrostatic Shield	Wiring Diagrams	Design Figures
3.0 ②	T2A533281S	10.38 (26.4)	12.37 (31.4)	7.47 (19.0)	75 (34.0)	W	0.75-1.25 (1.9-3.2)	STD.	25	F
6.0 ②	T2A533291S	11.83 (30.0)	14.17 (36.0)	8.82 (22.4)	140 (63.5)	W	0.75-1.25 (1.9-3.2)	STD.	25	F
9.0 ②	T2A533401S	14.03 (36.0)	17.77 (45.1)	11.52 (29.3)	180 (81.6)	W	0.75-1.25 (1.9-3.2)	STD.	25	F
15.0 ②	T3533411S	18.86 (47.9)	20.30 (51.6)	9.03 (22.9)	250 (113.0)	F ①	NA	STD.	25	I
15.0	T3015K0023B	25.50 (64.8)	24.39 (61.9)	19.37 (49.2)	300 (136.0)	F ①	NA	YES ③	26	E
30.0	T3030K0023B	25.50 (64.8)	24.39 (61.9)	19.37 (49.2)	360 (163.2)	F ①	NA	YES ③	26	E
45.0	T3045K0023B	25.50 (64.8)	24.39 (61.9)	19.37 (49.2)	500 (226.8)	F ①	NA	YES ③	26	E
75.0	T3075K0023B	29.41 (74.7)	28.15 (71.5)	22.37 (56.8)	600 (272.2)	F ①	NA	YES ③	26	E
112.5	T3112K0023B	35.47 (90.1)	31.90 (81.0)	26.88 (68.2)	938 (425.5)	F	NA	YES ③	26	E
150.0	T3150K0023B	41.52 (105.4)	32.90 (83.5)	29.87 (75.9)	1406 (637.8)	F	NA	YES ③	26	E
225.0	T3225K0023B	41.52 (105.4)	32.90 (83.5)	29.87 (75.9)	1500 (680.4)	F	NA	YES ③	26	E
300.0	T3300K0023B	45.60 (115.8)	39.50 (100.3)	35.50 (90.1)	1938 (879.0)	F	NA	YES ③	26	E
500.0	T3500K0023B	57.80 (147.0)	45.60 (115.8)	41.50 (105.4)	3344 (1516.8)	F	NA	YES ③	26	G
750.0	T3750K0023B	62.80 (159.5)	54.00 (137.1)	41.50 (105.4)	4260 (1932.3)	F	NA	YES ③	26	G

Notes: 3.0 kVA through 750.0 kVA provided with 120V lighting tap limited to 5% of nameplate rating.

① Wall mounting brackets are available for these sizes, refer to page 207.

② DOE 2016 exempt, encapsulated unit

③ Add "S" to part number

480 DELTA PRIMARY VOLTS — 480Y/277 SECONDARY VOLTS — MAY BE USED ON A 4 WIRE 480Y/277 VOLTS SUPPLY— 3Ø, 60 Hz

kVA	Catalog Number	Height (Inches)(Cm.)	Width (Inches)(Cm.)	Depth (Inches)(Cm.)	Weight (Lbs.)(Kg.)	Mounting Type (Wall)(Floor)	Knockouts (Inches)(Cm.)	Optional Electrostatic Shield	Wiring Diagrams	Design Figures
15.0 ②	T335000153S	18.86 (48.0)	20.30 (51.6)	9.03 (22.9)	250 (113.0)	F ①	NA	STD.	31	I
15.0	T3015K0053B	25.50 (64.8)	24.39 (61.9)	19.37 (49.2)	300 (136.0)	F ①	NA	YES ③	31	E
30.0	T3030K0053B	25.50 (64.8)	24.39 (61.9)	19.37 (49.2)	360 (163.3)	F ①	NA	YES ③	31	E
45.0	T3045K0053B	25.50 (64.8)	24.39 (61.9)	19.37 (49.2)	500 (226.8)	F ①	NA	YES ③	31	E
75.0	T3075K0053B	29.41 (74.7)	28.15 (71.5)	22.37 (56.8)	600 (272.2)	F ①	NA	YES ③	31	E
112.5	T3112K0053B	35.47 (90.1)	31.90 (81.0)	26.88 (68.2)	888 (402.8)	F	NA	YES ③	31	E
150.0	T3150K0053B	41.52 (105.4)	32.90 (83.5)	29.87 (75.9)	1444 (655.0)	F	NA	YES ③	31	E
225.0	T3225K0053B	41.52 (105.4)	32.90 (83.5)	29.87 (75.9)	1513 (686.3)	F	NA	YES ③	31	E
300.0	T3300K0053B	45.60 (115.8)	39.50 (100.3)	35.50 (90.1)	2000 (907.2)	F	NA	YES ③	31	E

① Wall mounting brackets are available for these sizes, refer to page 207.

② DOE 2016 exempt, encapsulated unit

③ Add "S" to part number

All Wiring Diagrams begin on page 197