



240 X 480 - 120/240
240 X 480 Primary Volts - 120/240 Secondary Volts - 1Ø
Industrial Control Transformer - Open Core & Coil

1047



Catalog #: TA83221

PRODUCT FEATURES

- Meets or exceeds UL, CSA, NEMA, and ANSI standards
- UL Listed and CSA Certified
- Meets NEC Article 450
- Constructed out of electrical lamination with precision wound coils
- Primary and secondary fuse kits easily adaptable
- Add suffix "F2" to catalog for factory installed 2 pole primary block
- Add suffix "F3" to catalog for factory installed 3 pole primary and secondary block
- Covered under Acme's 10 year limited warranty

BENEFITS

- Series parallel connecting links save time and costs
- Mounting plate adapts to various mounting dimensions
- Optional Secondary Fuse Kits available

UL STANDARD

UL 506

CSA STANDARD

C22.2 No 66

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

VA:	1500
Primary Voltage:	240 X 480
Secondary Voltage:	120/240
Frequency:	60 Hz
Max Temperature Rise:	80°C
UL Insulation Class:	130°C

PRODUCT MEASUREMENTS

Height (In./cm):	5.72 (14.5)
Width (In./cm):	6.75 (17.1)
Depth (In./cm):	8.80 (22.4)

CONFIGURATION

Mounting Type:	Floor
Primary Fuse Block:	PL112705
Wiring Diagram:	J

PACKAGING

Ship Weight (Lbs/Kg): 43 (19.5)

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No 66
CSA Listed: LR7357-16
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf