



220/440/550 - 90/110
220/440/550 Primary Volts - 90/110 Secondary Volts - 1Ø
Industrial Control Transformer - Open Core & Coil

1042



Catalog #: TB81000

PRODUCT FEATURES

- Meets or exceeds UL, CSA, NEMA, and ANSI standards
- UL Listed and CSA Certified
- Meets NEC Article 450
- Constructed out of electrical lamination with precision wound coils
- Primary and secondary fuse kits easily adaptable
- Add suffix "F2" to catalog for factory installed 2 pole primary block
- Add suffix "F4" to catalog for factory installed 2 pole primary and secondary fuse clips
- Covered under Acme's 10 year limited warranty

BENEFITS

- Series parallel connecting links save time and costs
- Mounting plate adapts to various mounting dimensions
- Molded terminal blocks allow easy ring terminal installation
- Optional Secondary Fuse Kits available

UL STANDARD

UL 506

CSA STANDARD

C22.2 No 66

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

VA:	50
Primary Voltage:	220/440/550
Secondary Voltage:	90/110
Frequency:	50/60 Hz
Max Temperature Rise:	80°C
UL Insulation Class:	130°C

PRODUCT MEASUREMENTS

Height (In./cm):	2.70 (6.8)
Width (In./cm):	3.00 (7.6)
Depth (In./cm):	4.56 (11.6)

CONFIGURATION

Mounting Type:	Floor
Primary Fuse Block:	PL112700
Wiring Diagram:	C

PACKAGING

Ship Weight (Lbs/Kg): 4 (1.8)

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No 66
CSA Listed: LR7357-16
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf