



440Δ - 220Y/127
440Δ Primary Volts - 220Y/127 Secondary Volts - 3Ø
Dry Type Distribution Transformer - Three Phase

1142



Catalog #: TF220255S

PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R epoxy encapsulated
- Floor Mounted
- Ground Studs for use with non-metallic conduit
- Aluminum Bus termination
- Covered under Acme's 10 year limited warranty

BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

UL STANDARD

UL 506

CSA STANDARD

C22.2 No. 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

KVA:	25.00
Primary Voltage:	440Δ
Secondary Voltage:	220Y/127
Frequency:	50 Hz
ANFC Taps:	-
BNFC Taps:	2
Taps % Steps:	5.0%
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

PRODUCT MEASUREMENTS

Height (In./cm):	25.50 (64.8)
Width (In./cm):	24.40 (62.0)
Depth (In./cm):	19.40 (49.3)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Floor
Weather Shield:	WSA1
Wiring Diagram:	73

PACKAGING

Ship Weight (Lbs/Kg): 375 (170.1)

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No. 47
CSA Listed: LR7357-32
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf