



440Δ - 220Y/127
440Δ Primary Volts - 220Y/127 Secondary Volts - 3Ø
Dry Type Distribution Transformer - Three Phase

1016



Catalog #: TF220505S

PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R with optional Weather Shield
- Floor Mounted
- Ground Studs for use with non-metallic conduit
- Aluminum Bus termination
- Covered under Acme's 10 year limited warranty

BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

UL STANDARD

UL 1561

CSA STANDARD

C22.2 No. 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

kVA:	50.00
Primary Voltage:	440Δ
Secondary Voltage:	220Y/127
Frequency:	50 Hz
ANFC Taps:	-
BNFC Taps:	2
Taps % Steps:	5.0%
Max Temperature Rise:	150°C
UL Insulation Class:	220°C

PRODUCT MEASUREMENTS

Height (In./cm):	29.41 (74.7)
Width (In./cm):	28.15 (71.5)
Depth (In./cm):	22.37 (56.8)

CONFIGURATION

Construction Type:	Ventilated
Mounting Type:	Floor
Weather Shield:	WSA2
Wiring Diagram:	73

PACKAGING

Ship Weight (Lbs/Kg): 437 (198.2)

COMPLIANCES

UL Standard: UL 1561
UL Listed: File E12547
CSA Standard: C22.2 No. 47
CSA Listed: LR7357-32
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf