



190/200/208/220 X 380/400/416/440 - 110/220
190/200/208/220 X 380/400/416/440 Primary Volts - 110/220 Secondary Volts - 1Ø - CE Marked
Dry Type Distribution Transformer - Single Phase

1002



Catalog #: TF279303S

PRODUCT FEATURES

- UL listed, CSA certified
- Fully encapsulated core and coil
- Meet CSA C802.2 Efficiency
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

UL STANDARD

UL 506

CSA STANDARD

C22.2 No. 47

CE

CE Marked

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

kVA:	5.00
Primary Voltage:	190/200/208/220 x 380/400/416/440
Secondary Voltage:	110/220
Frequency:	50/60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

PRODUCT MEASUREMENTS

Height (In./cm):	14.38 (36.5)
Width (In./cm):	10.31 (26.2)
Depth (In./cm):	7.13 (18.1)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall

Knockouts (In./Cm): 0.75-1.25 (1.9-3.2)
Wiring Diagram: 65

PACKAGING

Ship Weight (Lbs/Kg): 75 (34.0)

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No. 47
CSA Listed: LR7357-32
CE: CE Marked
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf