

GROUP I


**480 DELTA PRIMARY VOLTS — 480Y/277 SECONDARY VOLTS
MAY BE USED ON A 4 WIRE 480Y/277 VOLT SUPPLY — 3Ø, 60 Hz**

kVA	CATALOG NO.	APPROX. DIMENSIONS Inches (Cm.)			APPROX. SHIP WEIGHT Lbs. (Kg.)	TYPE MTG. W – Wall F – Floor	KNOCKOUTS Inches (Cm.)	WEATHER SHIELD P/N	Wiring Diagrams & Design Figures Begin on Page 122
		HEIGHT	WIDTH	DEPTH					
15.0	T335000153S	18.86 (48.0)	20.30 (51.6)	9.03 (22.9)	250 (113.0)	F ①	NA	NA	31-I
30.0	TP35000303S	29.41 (74.7)	28.15 (71.5)	22.37 (56.8)	325 (147.0)	F ①	NA	WSA2	31-E
45.0	TP135000453S	29.41 (74.7)	28.15 (71.5)	22.37 (56.8)	400 (181.0)	F ①	NA	WSA2	31-E
75.0	TP35000753S	29.41 (74.7)	28.15 (71.5)	22.37 (56.8)	600 (272.0)	F ①	NA	WSA2	31-E
112.5	TP35001123S	35.47 (90.1)	31.90 (81.0)	26.88 (68.3)	710 (322.0)	F	NA	WSA3	31-E
150.0	TP35001503S	41.52 (105.5)	32.90 (83.6)	29.87 (75.9)	1155 (524.0)	F	NA	WSA4	31-E
225.0	TP35002253S	41.52 (105.5)	32.90 (83.6)	29.87 (75.9)	1210 (548.8)	F	NA	WSA4	31-E
300.0	TP35003003S	45.60 (115.8)	39.50 (100.3)	35.50 (90.2)	1600 (726.0)	F	NA	WSA5	31-E

Notes: 15.0 kVA unit encapsulated (TP1 exempt), 30.0 through 300.0 kVA TP1 compliant

GROUP J

600 DELTA PRIMARY VOLTS — 208Y/120 SECONDARY VOLTS — 3Ø, 60 Hz

kVA	CATALOG NO.	APPROX. DIMENSIONS Inches (Cm.)			APPROX. SHIP WEIGHT Lbs. (Kg.)	TYPE MTG. W – Wall F – Floor	KNOCKOUTS Inches (Cm.)	WEATHER SHIELD P/N	Wiring Diagrams & Design Figures Begin on Page 122
		HEIGHT	WIDTH	DEPTH					
3.0	T2A-793301S	10.38 (26.4)	12.37 (31.4)	7.47 (19.0)	75 (34.0)	W	0.75-1.25 (1.9-3.2)	NA	28-F
6.0	T2A-793311S	11.83 (30.0)	14.17 (36.0)	8.82 (22.4)	140 (63.5)	W	0.75-1.25 (1.9-3.2)	NA	28-F
9.0	T2A-793321S	14.03 (36.0)	17.77 (45.1)	11.52 (29.3)	180 (81.6)	W	0.75-1.25 (1.9-3.2)	NA	28-F
15.0	T3-793331S	18.86 (47.9)	20.30 (51.6)	9.03 (22.9)	250 (113.0)	F ①	NA	NA	28-I
30.0	TP131023S	25.50 (64.8)	24.39 (61.9)	19.37 (49.2)	325 (147.0)	F ①	NA	WSA1	29-E
45.0	TP131033S	25.50 (64.8)	24.39 (61.9)	19.37 (49.2)	400 (181.0)	F ①	NA	WSA1	29-E
75.0	TP131043S	29.41 (74.7)	28.15 (71.5)	22.37 (56.8)	600 (272.0)	F ①	NA	WSA2	29-E
112.5	TP-131053S	35.47 (90.1)	31.90 (81.0)	26.88 (68.3)	750 (340.0)	F	NA	WSA3	29-E
150.0	TP-131063S	41.52 (105.5)	32.90 (83.6)	29.87 (75.9)	970 (440)	F	NA	WSA4	29-E
225.0	TP-131073S	41.52 (105.5)	32.90 (83.6)	29.87 (75.9)	1200 (544)	F	NA	WSA4	29-E
300.0	TP-130993S	45.60 (115.8)	39.50 (100.3)	35.50 (90.2)	1550 (703.0)	F	NA	WSA5	29-E
500.0	TP-131123S	57.84 (146.9)	45.00 (114.3)	41.50 (105.4)	2480 (1125.0)	F	NA	WSA7	29-E
750.0	TP-131133S	62.84 (159.6)	54.00 (137.2)	41.50 (105.4)	3600 (1633.0)	F	NA	WSA6	29-E

Notes: 3.0 through 15.0 kVA encapsulated (TP1 exempt), 30.0 through 75.0 kVA TP1 compliant

① Wall mounting brackets are available for these sizes, refer to page 133.