



240X480 - 120/240  
240 X 480 Primary Volts - 120/240 Secondary Volts - Four Windings - 1Ø  
Dry Type Distribution Transformer - Single Phase

1007



Catalog #: TP530203S

**PRODUCT FEATURES**

- UL listed, CSA certified
- Meet DOE 2016 efficiency requirements
- UL Type 3R with optional Weather Shield
- Floor Mounted
- Ground Studs for use with non-metallic conduit
- Copper Bus termination
- Covered under Acme's 10 year limited warranty

**BENEFITS**

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

**UL STANDARD**

UL 506

**CSA STANDARD**

C22.2 No. 47

**WARRANTY**

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

**GENERAL PRODUCT INFORMATION**

kVA:	50.00
Primary Voltage:	240 X 480
Secondary Voltage:	120/240
Frequency:	60 Hz
ANFC Taps:	2
BNFC Taps:	4
Taps % Steps:	2.5%
Max Temperature Rise:	150°C
UL Insulation Class:	220°C

**PRODUCT MEASUREMENTS**

Height (In./cm):	25.50 (64.8)
Width (In./cm):	24.39 (61.9)
Depth (In./cm):	19.37 (49.2)

**CONFIGURATION**

Construction Type:	Ventilated
Mounting Type:	Floor
Weather Shield:	WSA1
Wiring Diagram:	5

**PACKAGING**

Ship Weight (Lbs/Kg): 350 (158.8)

**COMPLIANCES**

UL Standard: UL 506  
UL Listed: File E79947  
CSA Standard: C22.2 No. 47  
CSA Listed: LR7357-32  
Warranty: Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)