

FASTENERS

THREADED STUDS

PRODUCT DESCRIPTION

Threaded studs are available in 1/4"-20 and 3/8"-16 thread diameters with a variety of thread and shank lengths for use in concrete, some types of concrete block, and A36 or A572 structural steel. They are used for applications where it may be desirable to remove the fixture, where shimming may be required or for suspending sprinkler systems.

The shank diameter for the threaded studs is 0.145" for the 1/4"-20 diameter and 0.205" for the 3/8"-16 diameter. Both sizes have a specially designed point to allow proper penetration into the base material. Knurled shank designs are available to increase performance in steel base materials. A plastic flute is mounted over the point to retain the drive pin in the fasteners guide of the tool providing guidance during the driving operation. On the 1/4"-20 threaded studs a plastic cap is also provided to protect the threads of the fastener during the driving process as well as providing guidance during installation.

FASTENERS SIZE

1/4"-20 Threaded Studs

Cat.No.	Thread Length	Shank Length	Shank Dia.	Standard Box	Std. Carton	Wt./100
50322-PWR	3/4"	1/2" (K)	0.145"	100	1,000	1.1
50326-PWR	3/4"	3/4"	0.145"	100	1,000	1.2
50328-PWR	1/2"	1"	0.145"	100	1,000	1.2
50330-PWR	3/4"	1"	0.145"	100	1,000	1.4
50336-PWR	3/4"	1-1/4"	0.145"	100	1,000	1.5

(K) = knurled



3/8"-16 Threaded Studs

Cat.No.	Thread Length	Shank Length	Shank Dia.	Standard Box	Std. Carton	Wt./100
50340-PWR	1-1/4"	3/4" (K)	0.205"	100	1,000	3.6
50342-PWR	1-1/4"	1"	0.205"	100	1,000	3.8
50344-PWR	1-1/4"	1-1/4"	0.205"	100	1,000	3.8

(K) = knurled



ROD HANGERS

PRODUCT DESCRIPTION

Rod Hangers and Post-Nut hangers for suspending electrical metal tubing (EMT), mechanical and electrical components from concrete and steel. Rod Hangers and Post-Nut Clip accept either 1/4" or 3/8" threaded rod.

Spiral CSI and 8mm Head Drive Pins with Rod Hanger Clip

Catalog Number	Description	Shank Diameter	Standard Box	Standard Carton
50215-PWR	32mm (1-1/4") Spiral CSI Pin with 1/4"-20 Rod Hanger	0.157"	100	1,000
50219-PWR	32mm (1-1/4") Pin with 1/4"-20 Rod Hanger	0.145"	100	1,000
50221-PWR	32mm (1-1/4") Pin with 3/8"-16 Rod Hanger	0.145"	100	1,000



.300 Head Drive Pins with Post Nut Rod Hanger Clip

Catalog Number	Description	Shank Diameter	Standard Box	Standard Carton
50376-PWR	1-1/8" (29mm) Head Pin with Domed Right Angle Clip Rod Hanger	0.145"	100	1,000
50378-PWR	1-1/4" (32mm) Head Pin with Domed Right Angle Clip Rod Hanger	0.145"	100	1,000



**POWDER ACTUATED
THREADED STUDS. ROD HANGERS**