


# WP2H150QT

Mid sized wallpack. All aluminum precision die cast construction with tempered glass refractor. Lamp supplied.

Color: Bronze

Weight: 18.4 lbs



## Lamp Info

Type: ED17  
 Watts: 150  
 Shape/Size: N/A  
 Base: N/A  
 ANSI: N/A  
 Hours: 10,000  
 Lamp Lumens: 12,500  
 Efficacy: 68 LPW

## Ballast Info

Type: CWA-HPF QT  
 120V: 1.1/1.6  
 208V: .6/.9  
 240V: .5/.8  
 277V: .5/.7  
 Input Watts: 185W  
 Efficiency: 81%

## Technical Specifications

### UL Listing:

Suitable for wet locations. HID fixtures can be wired with 90 C supply wiring if supply wires are routed 3" away from ballast.

### Housing:

Die cast aluminum, 1/2" NPS tapped holes top, both sides and back for conduit or photocontrol. Hinged refractor frame. Continuous silicone rubber gasket.

### Reflector:

Specular anodized aluminum, removable for installation. Symmetrical light pattern maximizes distance between fixtures.

### Cutoff Lens:

Tempered glass.

### Refractor:

Prismatic optics designed to minimize glare and throw light down and out. Heat resistant borosilicate glass.

### Finish:

Chip and fade resistant polyester powder coating.

### Quad Tap:

Fixture works with 120, 208, 240 and 277 Volts

### Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws