



Representative

Catalog Number: PAA1093
Product ID: 7TAA267200R0002
UPC Number: 78378632998
EAN Number: 05414363156666
Status: Active

Galvanized Steel Parallel Groove Clamp - Conductor material ACSR 1/0 AWG - ACSR/Copper/Aluminum 6 AWG

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Parallel-Groove Clamp
Special Features	High-Strength, Heat-Treated Cast Aluminum Alloy provides Secure Connections. Galvanized Steel Carriage Bolt, Nut and Lockwasher included. Dual-Rated for use on Aluminum, ACSR and Copper Conductors.
Application	Securing Conductors
Size	Bolt Hex-Head 9/16 inch, Bolt Size 3/8 inch, Height 2-15/32 X Length 2 X Width 1-3/4 inch
Connection	Bolted
Conductor Range	MAIN: 1/0 - 6 ACSR WITH ARMOR 336 - 1/0 ACSR 400 - 1/0 AL, TAP: 1/0 - 8 ACSR 1/0 - 8 AL
Number Of Conductors	2
Material	Aluminum
Insulation	None
Mounting	None
Environmental Conditions	All Seasons / Conditions

Packaging

Outer Quantity	25
Outer Dimensions (inches)	8.3x7.4x6.6
Weight Uom	23.5 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com