


# STL110H

STEALTH 110 Sensor with twin precision die cast H101 Deluxe shielded floods pre-wired and assembled on universal CU4 cover plate.

Color: Bronze

Weight: 5.0 lbs



## Technical Specifications

### UL Listing:

Suitable for wet locations

### Power Consumption:

1 watt

### Time Adjustment:

5 seconds to 12 minutes

### Surge Protection:

Withstands up to 6000 volts

### Wide Sensitivity Control:

Adjustable from 100% to 30%

### Temperature Compensation:

Sensitivity adjusts automatically for consistent detection in hot and cold ambient temperatures

### Wall Switch Manual Override:

Two flip logic prevents activation by momentary power outages. Override resets to auto at dawn. No extra wiring needed

### LED Detection Indicator:

Shows when sensor is detecting in daytime and glows red at night for "on-guard" deterrence

### Advanced Detection Logic:

Minimizes false triggers

### Color Matched Lens:

Dark lens with bronze units, white lens with white units

### RF Immunity:

Circuits fully shielded for maximum radio frequency immunity

### Horizontal Lock, No-tool Joints:

Keeps sensing pattern level for fast, error-free installation

### Photoelectric Control:

Deactivates lights during daylight. Fully adjustable for 24 hour operation or custom applications

### Floodlights:

Precision die cast aluminum. 1/2" NPS threaded arm with serrated locking swivel fits all standard mounting boxes and covers

### Lamp:

Accepts PAR38 lamps, 150 watt max. Lamps are not supplied.

### Voltage:

120 Volts AC 60 Hertz

### Lens Mask:

Customized press apply lens mask included to reduce coverage easily

### Detection:

200° view

### Switching Capacity:

1000 watts incandescent @ 120 volts, 8 amps

### Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws

### Warranty:

10 year sensor warranty