

→ Motor Model Details

AC NEMA MOTOR » GENERAL PURPOSE THREE PHASE



Catalog Number: E829
Model Number: 145TTTN4076
List Price: Price Unavailable
Multiplier Symbol: E1
Normally Stocked: Y

Technical Data

Dim Drawing: [A-100655-625](#)
Conn Diagram: [A-EE7308](#)
[Certification Data Sheet](#)
[Certification Data Sheet in PDF](#)
[Installation, Maintenance, Operation Manual](#)

****Motor Nameplate Shows 60 and 50 Hertz Information****

60 Hertz				50 Hertz			
HP	1	Voltage	230/460	HP	3/4	Voltage	190/380
kW	0.75	FL Amps	3.3/1.65	kW	0.56	FL Amps	3.4/1.7
RPM	1200			RPM	1000		
FL Eff	80 %	SF	1.15	FL Eff	79 %	SF	1.15

Phase 3
Frame 145T
Enclosure TENV
Mounting Rigid
Orientation HORIZONTAL
Assembly F1 (F2 Modification Available)
Drive End Bearing BALL
Opposite End Bearing BALL
Drive End Bearing Size 6205
Opposite End Bearing Size 6203
Weight 58 LB lbs

Insulation Class F
Duty CONTINUOUS
Ambient 40
NEMA Design B
Starting Type ACROSS THE LINE
KVA Code J
IP Code 43

CE Y

UL Recognized Construction

CSA Y

Thermal Protection

**Drawings on the website are current at the time of inquiry. All copies made of drawings are considered "Uncontrolled" at time of print. "Uncontrolled Copy" means that Marathon Electric has no mechanism or process in place to notify the user of changes made subsequent to time of download.