



Representative

Catalog Number: AL12P
Product ID: 7TAA268500R0002
UPC Number: 78378608657
Status: Active

Aluminum Two-Hole Lug - Straight Long Barrel, Wire Range 4/0 ASCR, 4/0 Stranded, 1/2 Inch Bolt Size, Blind-End, Mechanical Dies: 840, K840, 845, TX, Hydraulic Dies: 840, B49EA, EEI, 11A, K840, 249, 76, CSA 24, Tin-Plated

North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Blackburn
Type	Compression Connector
Special Features	PreFilled with Compound. Complete Die and Crimp information clearly indented on each lug. Installed with standard tools and dies. Use 1/2 inch mounting hardware for all sizes. Tin-Plated.
Application	For Aluminum and Copper Conductor.
Cable Size	4/0 ASCR, 4/0 Stranded
Number Of Holes	2
Material	Aluminum
Mounting	NEMA Standard Mounting Holes
Connection	Crimp

European Specifications (ETIM)

ETIM	EC001053 Crimp cable lug for aluminium conductors
Material	Aluminium
Number of fixing holes	2
Sleeve form	Long

Packaging

Inner Quantity	25
Inner Dimensions (inches)	7.13x6.13x4.81
Outer Quantity	150
Outer Dimensions (inches)	21x11x8
Weight Uom	25.63 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com