

## FLEXIBLE ELECTRICAL CORD OR CABLE TO CORD GRIP SELECTION TABLE

Cord Type SJ-SJTO SJO	Cord OD	Hub Size	Straight Cord Grip	Alternate Straight	90 Degree Cord Grip	45 Degree Cord Grip
—	.125-.188	1/2"	RSR-1003	RSR-103	RSR-9103	RSR-45103
—	.125-.188	3/4"	RSR-2103	—	—	—
—	.188-.250	1/2"	RSR-1004	RSR-104	RSR-9104	RSR-45104
—	.188-.250	3/4"	RSR-2104	—	—	—
18/2	.290	1/2"	RSR-1005	RSR-105	RSR-9105	RSR-45105
18/2	.290	3/4"	RSR-2105	—	—	—
18/3	.320	1/2"	RSR-1006	RSR-106	RSR-9106	RSR-45106
18/3	.320	3/4"	RSR-2106	—	—	—
18/4	.335	1/2"	RSR-1006	RSR-106	RSR-9106	RSR-45106
18/4	.335	3/4"	RSR-2106	—	—	—
16/2	.320	1/2"	RSR-1006	RSR-106	RSR-9106	RSR-45106
16/2	.320	3/4"	RSR-2106	—	—	—
16/3	.340	1/2"	RSR-1006	RSR-106	RSR-9106	RSR-45106
16/3	.340	3/4"	RSR-2106	—	—	—
16/4	.385	1/2"	RSR-1007	RSR-107	RSR-9107	RSR-45107
16/4	.385	3/4"	RSR-2107	—	—	—
14/2	.350	1/2"	RSR-1006	RSR-106	RSR-9106	RSR-45106
14/2	.350	3/4"	RSR-2106	—	—	—
14/3	.375	1/2"	RSR-1007	RSR-107	RSR-9107	RSR-45107
14/3	.375	3/4"	RSR-2107	—	—	—
14/4	.415	1/2"	RSR-1007	RSR-107	RSR-9107	RSR-45107
14/4	.415	3/4"	RSR-2107	—	—	—

Cord Type S-STO-SO	Cord OD	Hub Size	Straight Cord Grip	Alternate Straight	90 Degree Cord Grip	45 Degree Cord Grip
18/2	.345	1/2"	RSR-1006	RSR-106	RSR-9106	RSR-45106
18/2	.345	3/4"	RSR-2106	—	—	—
18/3	.365	1/2"	RSR-1006	RSR-106	RSR-9106	RSR-45106
18/3	.365	3/4"	RSR-2106	—	—	—
18/4	.390	1/2"	RSR-1007	RSR-107	RSR-9107	RSR-45107
18/4	.390	3/4"	RSR-2107	—	—	—
16/2	.370	1/2"	RSR-1006	RSR-106	RSR-9106	RSR-45106
16/2	.370	3/4"	RSR-2106	—	—	—
16/3	.390	1/2"	RSR-1007	RSR-107	RSR-9107	RSR-45107
16/3	.390	3/4"	RSR-2107	—	—	—
16/4	.415	1/2"	RSR-107	RSR-1207	RSR-9107	RSR-45107
16/4	.415	3/4"	RSR-2107	—	—	—
14/2	.500	1/2"	RSR-109	RSR-1209	RSR-9109	RSR-45109
14/2	.500	3/4"	RSR-2109	RSR-209	RSR-9209	RSR-45209
14/2	.500	1"	RSR-309	—	RSR-9309	RSR-45309
14/3	.530	1/2"	RSR-109	RSR-1209	RSR-9109	RSR-45109
14/3	.530	3/4"	RSR-2109	RSR-209	RSR-9209	RSR-45209
14/3	.530	3/4"	RSR-209	—	RSR-9210	RSR-45210
14/3	.530	1"	RSR-309	RSR-310	RSR-9309	RSR-45309
14/4	.570	1/2"	RSR-110	RSR-1211	RSR-9110	RSR-45110
14/4	.570	3/4"	RSR-2110	RSR-211	RSR-9210	RSR-45210
14/4	.570	1"	RSR-310	RSR-311	RSR-9310	RSR-45310
12/2	.575	1/2"	RSR-110	RSR-1210	RSR-9110	RSR-45110
12/2	.575	3/4"	RSR-2110	RSR-210	RSR-9210	RSR-45210
12/2	.575	1"	RSR-310	—	RSR-9310	RSR-45310
12/3	.600	1/2"	RSR-110	RSR-1210	RSR-9110	RSR-45110

## FLEXIBLE ELECTRICAL CORD OR CABLE TO CORD GRIP SELECTION TABLE

Cord Type S-STO-SO	Cord OD	Hub Size	Straight Cord Grip	Alternate Straight	90 Degree Cord Grip	45 Degree Cord Grip
12/3	.600	3/4"	RSR-2110	RSR-210	RSR-9210	RSR-45210
12/3	.600	1"	RSR-310	RSR-310	RSR-9310	RSR-45310
12/4	.650	1/2"	RSR-1211	—	—	—
12/4	.650	3/4"	RSR-211	RSR-2311	RSR-9211	RSR-45211
12/4	.650	1"	RSR-311	—	RSR-9311	RSR-45311
10/2	.625	1/2"	RSR-1211	—	—	—
10/2	.625	3/4"	RSR-211	RSR-2311	RSR-9211	RSR-45211
10/2	.625	1"	RSR-311	—	RSR-9311	RSR-45311
10/3	.660	1/2"	RSR-1211	—	—	—
10/3	.660	3/4"	RSR-211	RSR-2311	RSR-9211	RSR-45211
10/3	.660	1"	RSR-311	—	RSR-9311	RSR-45311
10/4	.710	1/2"	RSR-1212	—	—	—
10/4	.710	3/4"	RSR-212	RSR-2312	RSR-9212	RSR-45212
10/4	.710	1"	RSR-312	—	RSR-9312	RSR-45312
8/2	.675	1/2"	RSR-1211	—	—	—
8/2	.675	3/4"	RSR-211	RSR-2311	RSR-9211	RSR-45211
8/2	.675	1"	RSR-311	—	RSR-9311	RSR-45311
8/3	.725	1/2"	RSR-1212	—	—	—
8/3	.725	3/4"	RSR-212	RSR-2312	RSR-9212	RSR-45212
8/3	.725	1"	RSR-312	—	RSR-9312	RSR-45312
8/4	.780	1/2"	RSR-1213	—	—	—
8/4	.780	3/4"	RSR-213	RSR-2313	RSR-9213	RSR-45213
8/4	.780	1"	RSR-313	RSR-3514	RSR-9313	RSR-45313
8/4	.780	1 1/4"	RSR-414	—	RSR-9414	RSR-45414
8/4	.780	1 1/2"	RSR-514	—	RSR-9514	RSR-45514
6/2	.795	1"	RSR-313	RSR-3514	RSR-9313	RSR-45313
6/2	.795	1 1/4"	RSR-414	—	RSR-9414	RSR-45414
6/2	.795	1 1/2"	RSR-514	—	RSR-9514	RSR-45514
6/3	.865	1"	RSR-314	RSR-3514	RSR-9314	RSR-45314
6/3	.865	1 1/4"	RSR-414	—	RSR-9414	RSR-45414
6/3	.865	1 1/2"	RSR-514	—	RSR-9514	RSR-45514
6/4	.900	1"	RSR-315	RSR-3516	RSR-9315	RSR-45315
6/4	.900	1 1/4"	RSR-416	—	RSR-9416	RSR-45416
6/4	.900	1 1/2"	RSR-516	—	RSR-9516	RSR-45516
4/3	.975	1"	RSR-3516	—	—	—
4/3	.975	1 1/4"	RSR-416	—	RSR-9416	RSR-45416
4/3	.975	1 1/2"	RSR-516	—	RSR-9516	RSR-45516
4/4	1.100	1"	RSR-3518	—	—	—
4/4	1.100	1 1/4"	RSR-418	—	RSR-9418	RSR-45418
4/4	1.100	1 1/2"	RSR-518	—	RSR-9518	RSR-45518
2/3	1.170	1"	RSR-3520	—	—	—
2/3	1.170	1 1/4"	RSR-420	—	RSR-9420	RSR-45420
2/3	1.170	1 1/2"	RSR-520	—	RSR-9520	RSR-45520
2/4	1.290	1"	RSR-3522	—	—	—
2/4	1.290	1 1/4"	RSR-422	—	RSR-9422	RSR-45422
2/4	1.290	1 1/2"	RSR-522	—	RSR-9522	RSR-45522

**NOTE:** If a Mesh Grip is required, add letter 'E' to end of Remke part number. This chart is based on the cable diameters shown.

The actual diameter of the cable being used may require the next larger or smaller cord grip bushing.

Cable diameters vary between manufacturers and because cable manufacturers must allow tolerance, their published data should be checked.

The bushing I.D. should be larger than, but as close as possible to, the cable O.D.