



Actual

Catalog Number: AMTD35064
Product ID: 7TAH006400R0057
UPC Number: 78378652417
Status: Active

AMT 4 Multi-Port Both Sides PVC Connector, Ultraviolet Resistant, Wire Range 350 kcmil-6 Str, Length 4.26 Inches, Width 3.0 Inches, Height 2.5 Inches, Hex Size 3/8 Inch, Black Insulation

- PVC Insulation eliminates insulation failures and reduces outage costs. Removable port and screw plugs.
- Compact design provides space efficiencies.
- All cable entry are equipped with an anti-oxidation compound.

North American Specifications (UNSPSC)

UNSPSC	39121410 Terminal blocks
IGCC	4547 Terminal blocks
Brand Name	Blackburn
Type	AMT Connectors
Special Features	PVC Insulation eliminates insulation failures and reduces outage costs. Removable port and screw plugs.
Standard	UL E9809
Wire Size	350 kcmil-6 Str
Voltage Rating	600V
Material	Aluminum
Color	Black

Packaging

Outer Quantity	10
Outer Dimensions (inches)	13.187x7.75x7
Weight Uom	0.73 lbs. Each

Documents / Support Tools

Technical Data Sheet CA Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com