

R frame, galvanized fittings

R 型框架，镀锌挡板 | R-Rahmen, feuerverzinkte Beschläge | Marco R, componentes galvanizados | Bague R, acier galvanisé



R 100 galv

R 125 galv

R 127 galv

R 150 galv

R 200 galv

Parts needed for a complete solution



page 25



page 165

Accessories



page 178



page 181

See also Installation guidelines on page 189.

RATINGS Fire: A-Class, H-Class, EI 60/120, UL1479 Water pressure: 4 bar Gas pressure: 2.5 bar

CN DE ES FR EN	框架 Rahmen Marco Bague Frame	密封空间 (毫米) Belegraum (mm) Espacio útil de sellado (mm) Espace de remplissage (mm) Packing space (mm)	孔径 Für Lochdurchmesser Ø (毫米) Ø (英寸) Para diámetro de hueco Ø (mm) Ø (pulgadas) Pour diamètre de trou Ø (mm) Ø (pouces) For hole diameter Ø (mm) Ø (in)		重量 (千克) (磅) Gewicht (kg) (lb) Peso (kg) (libra) Poids (kg) (lb) Weight (kg) (lb)		货号 Art.-Nr. N° art. N° d'article Art. No.
			Ø (mm)	Ø (in)	(kg)	(lb)	
	R 100 galv	60 x 60	100-102	3.937-4.016	0.7	1.499	R000001001018
	R 125 galv	80 x 80	125-127	4.921-5.000	1.1	2.447	R000001251018
	R 127 galv	80 x 80	127-129	5.000-5.079	1.1	2.447	R000001271018
	R 150 galv	90 x 90	150-152	5.906-5.984	1.6	3.638	R000001501018
	R 200 galv	120 x 120	200-202	7.874-7.953	2.6	5.732	R000002001018