



Actual

Catalog Number: 2B350
Product ID: 7TAH006160R0011
UPC Number: 78378640004
Status: Active

Copper Type 2B - Two-Bolt Connector without Spacer for Wire Range Main: 4/0 Str. - 350 kcmil Tap: 4 Sol. - 350 kcmil , Bolt Size 3/4

- Castings and bolts of high-strength copper alloy. Removable cap.
- UL 486A listed for copper conductor only.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Two-Bolt Connector
Special Features	Castings and bolts of high-strength copper alloy. Removable cap.
Standard	UL E9809
Material	Copper
Conductor Range (Main/Primary)	4/0 Str. - 350 kcmil
Conductor Range (Tap/Secondary)	4 Sol. - 350 kcmil
Bolt Size	42798

European Specifications (ETIM)

ETIM	EC000491 Earth terminal clamp
Suitable for	Round conductor
Material	Copper

Packaging

Inner Quantity	1
Outer Quantity	25
Outer Dimensions (inches)	7.25x8.25x6.75
Weight Uom	65.63 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com