



Product Number: 25272

Order Abbreviation: F72T12/CW/VHO

General Description: 160W, 72" MOL, T12 VHO (1500 mA) rapid start fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI

Product Information

Abbrev. With Packaging Info.	F72T12CWVHO 15/CS 1/SKU
Actual Length (in)	69.909
Actual Length (mm)	1775.69
Average Rated Life (hr)	10000
Base	Recessed Double Contact
Bulb	T12
Color Rendering Index (CRI)	60
Color Temperature/CCT (K)	4200
Diameter (in)	1.593
Diameter (mm)	40.46
Family Brand Name	VHO
Industry Standards	ANSI C78.81 - 2001
Initial Lumens at 25C	10600
Mean Lumens at 25C	7420
Mean Lumens at 35C	7420
Nominal Length (in)	72.000
Nominal Length (mm)	1828.80
Nominal Wattage (W)	160.00

Footnotes

- Approximate initial lumens after 100 hours operation.
- The life ratings of fluorescent lamps are based on 3 hr. burning cycles under specified conditions and with ballast meeting ANSI specifications. If burning cycle is increased, there will be a corresponding increase in the average hours life.
- Minimum starting temperature is a function of the ballast; consult the ballast manufacturer.
- Average life rating at 12 hours operation per start is 15,000 hours.