

# Miniature Lamp Specifications

Line No.	Lamp No.	Base	Des. Volts	Amps or Watts	MSCP	Fil. Type	MOL (inch)	LCL (inch)	Ave Life (Hrs)	Primary Application	Fig. No.
<b>B-3 1/2 Bulb</b>											
1	PR4	S.C. Miniature Flanged	2.33	.27	.40	C-2R	1.25	.25	10	Flashlight-2 C Cells	1
2	PR2	S.C. Miniature Flanged	2.38	.50	.80	C-2R	1.25	.25	15	Flashlight-2 D Cells	1
3	K2	S.C. Miniature Flanged	2.4	.70	1.20	C-2R	1.25	.25	15	Flashlight-Krypton 2 Cells	1
4	KPR102	S.C. Miniature Flanged	2.4	.70	1.30	C-2R	1.25	.25	15	Flashlight-Krypton 2 Cells	1
5	PR6	S.C. Miniature Flanged	2.47	.30	.45	C-2R	1.25	.25	30	Flashlight-2 D Cells	1
6	PR3	S.C. Miniature Flanged	3.57	.50	1.5	C-2R	1.25	.25	15	Flashlight-3 D Cells	1
7	K3	S.C. Miniature Flanged	3.6	.90	3.4	C-2R	1.25	.25	15	Flashlight-Krypton 3 Cells	1
8	KPR103	S.C. Miniature Flanged	3.6	.75	2.7	C-2R	1.25	.25	20	Flashlight-Krypton 3 Cells	1
9	PR7	S.C. Miniature Flanged	3.7	.30	.90	C-2R	1.25	.25	30	Flashlight-3 Cells	1
10	PR30	S.C. Miniature Flanged	3.75	.86	2.25	C-2R	1.25	.25	40	Flashlight-3 Cells	1
11	PR13	S.C. Miniature Flanged	4.75	.50	2.0	C-2R	1.25	.25	15	Flashlight-4 F Cells	1
12	K13	S.C. Miniature Flanged	4.75	.70	4.0	C-2R	1.25	.25	15	Flashlight-Krypton 4 Cells	1
13	KPR113	S.C. Miniature Flanged	4.8	.75	4.06	C-2R	1.25	.25	20	Flashlight-Krypton 4 Cells	1
14	PR15	S.C. Miniature Flanged	4.82	.50	2.0	C-2R	1.25	.25	30	Hand Lantern-8 F Cells	1
15	PR17	S.C. Miniature Flanged	4.9	.30	1.2	C-2R	1.25	.25	30	Hand Lantern-8 F Cells	1
16	K12	S.C. Miniature Flanged	5.95	.70	7.5	C-2R	1.25	.25	8	Hand Lantern-Krypton 8 F Cells	1
17	PR12	S.C. Miniature Flanged	5.95	.50	3.0	C-2R	1.25	.25	15	Flashlight-5 D Cells	1
18	PR18	S.C. Miniature Flanged	7.2	.55	4.2	C-2R	1.25	.25	3	Flashlight-6 D Cells	1
19	PR20	S.C. Miniature Flanged	8.63	.50	5.0	C-2R	1.25	.25	15	Flashlight-7 D Cells	1
20	PR16	S.C. Miniature Flanged	12.5	.25	2.7	C-2R	1.25	.25	50	Auto Spotlight	1
<b>B-6 Bulb</b>											
21	210	D.C. Bayonet	6.5	1.78	15	C-6	1.75	1.06	100	Instrument	3
22	1003	S.C. Bayonet	12.8	.94	15	C-6	1.75	1.06	100	Auto Interior	2
23	1004	D.C. Bayonet	12.8	.94	15	C-6	1.75	1.06	100	Auto Interior	3
24	104	D.C. Bayonet	12.8	1.0	12	C-6	1.75	1.06	500	Auto Interior	3
25	105	S.C. Bayonet	12.8	1.0	12	C-6	1.75	1.06	500	Auto Interior	2
26	1309	S.C. Bayonet	28.0	.52	15	2C-2R	1.75	1.06	300	Aircraft Interior	2
27	1308	S.C. Bayonet	28.0	.56	16	CC-8	1.75	1.06	2,000	Aircraft Interior	2




Fig. 1 (C-2R filament shown)




Fig. 2 (C-6 filament shown)




Fig. 3 (C-6 filament shown)

Some lamp pictures are not to scale. Filament and L.C.L. may vary by part number. For filament identification see page 6.

THE PRODUCTS SHOWN REPRESENT ONLY A SMALL PORTION OF OUR STOCK  
PLEASE CALL IF THE PRODUCT YOU NEED IS NOT LISTED  
949/452-0900 • 800/8-LIGHTS • FAX: 800-255-3141