



GE
Lighting

42793 - F70T8/840PLYUX

GE T8

GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight
	Linear
Bulb	T8
Base	Medium Bi-Pin (G13)
Rated Life	20000.0 hrs
Bulb Material	Soda lime
Primary Application	Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	6300.0
Mean Lumens	5985.0
Nominal Initial Lumens per Watt	90
Color Temperature	4100.0 K
Color Rendering Index (CRI)	85.0

ELECTRICAL CHARACTERISTICS

Wattage	70.0
Lamp Current	0.7 A

DIMENSIONS

Maximum Overall Length (MOL)	72.0000 in(1828.8 mm)
Nominal Length	70.000 in(1778.0 mm)
Bulb Diameter (DIA)	1.000 in(25.4 mm)
Max Base Face to Base Face (A)	69.720 in(1770.9 mm)
Face to End of Opposing Pin (B) (MIN)	69.630 in(1768.6 mm)
Face to End of Opposing Pin (B) (MAX)	69.720 in(1770.9 mm)

PRODUCT INFORMATION

Product Code	42793
Description	F70T8/840PLYUX
Standard Package	Case
Standard Package GTIN	10043168427934
Standard Package Quantity	25
Sales Unit	Case
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	25
UPC	043168427937