

MINIATURE & AUTOMOTIVE LAMPS

| Ordering Abbreviation | Product Number | Bulb | Base | Avg Rated Life (hrs) | Approx Lumens | Amps | Design Voltage (V) | Pkg Qty | MOL (in) | Footnotes |
|-----------------------|----------------|--------------|-----------------|----------------------|-----------------|-------------|--------------------|---------|----------|-----------|
| 1076 | 36183 | S8 | DC Bayonet | 200 | 402.12 | 1.8 | 13 | 1000 | 2 | |
| 1130 | 36237 | S8 | DC Bayonet | 200 | 263.89 | 2.63 | 6 | 1000 | 2 | |
| 1141 | 36377 | S8 | SC Bayonet | 1000 | 263.89 | 1.44 | 13 | 1000 | 2 | |
| 1156 | 36521 | S8 | SC Bayonet | 1200 | 402 | 2.1 | 13 | 1000 | 2 | |
| 1156 | 36521 | S8 | SC Bayonet | 1200 | 402 | 2.1 | 13 | 1000 | 2 | |
| 1157 | 36561 | S8 | DC Index | 1200 5000 | 402.00 38.00 | 2.1 0.6 | 13 14 | 1000 | 2 | |
| 120MB | 34503 | T2.5 | Mini Bayonet | 10000 | 4.52 | 0.025 | 120 | 1000 | 1.19 | |
| 120MB | 34503 | T2.5 | Mini Bayonet | 10000 | 4.52 | 0.025 | 120 | 1000 | 1.19 | |
| 120MB 6W | 34513 | T2.5 | Mini Bayonet | 3000 | 18 | 0.052 | 120 | 1000 | 1.19 | |
| 120PC | 34519 | T2 | Bipin | 7500 | | 0.025 | 120 | 1000 | 1.125 | 1 |
| 120PSB | 34557 | T2 | Slide Base # 5 | 10000 | | 0.025 | 120 | 1000 | 1.11 | |
| 120PSB | 34557 | T2 | Slide Base # 5 | 10000 | | 0.025 | 120 | 1000 | 1.11 | |
| 12PSB | 32983 | T2 | Slide Base # 5 | 12000 | | 0.17 | 12 | 1000 | 1.11 | |
| 161 | 34691 | T3.25 | W2.1x9.2D | 4000 | 12.57 | 0.19 | 14 | 1000 | 1.054 | |
| 168 | 34711 | T3.25 | W2.1x9.2D | 1500 | 37.7 | 0.35 | 14 | 1000 | 1.054 | |
| 17 | 33061 | T1.75 | W2.1x4.9D | 5000 | 8.17 | 0.065 | 28 | 1000 | 0.8 | |
| 1815 | 37329 | T3.25 | Mini Bayonet | 3000 | 17.59 | 0.2 | 14 | 1000 | 1.19 | |
| 1816 | 37333 | T3.25 | Mini Bayonet | 1000 | 37.7 | 0.33 | 13 | 1000 | 1.19 | |
| 1819 | 37351 | T3.25 | Mini Bayonet | 2500 | 4.27 | 0.04 | 28 | 1000 | 1.19 | |
| 1820 | 37355 | T3.25 | Mini Bayonet | 1000 | 20.11 | 0.1 | 28 | 1000 | 1.19 | |
| 1822 | 37367 | T3.25 | Mini Bayonet | 1000 | 26.39 | 0.1 | 36 | 1000 | 1.19 | |
| 1829 | 37377 | T3.25 | Mini Bayonet | 1000 | 12.57 | 0.07 | 28 | 1000 | 1.19 | |
| 1835 | 37387 | T3.25 | Mini Bayonet | 5000 | 13.82 | 0.05 | 55 | 1000 | 1.19 | |
| 1847 | 37391 | T3.25 | Mini Bayonet | 5000 | 4.78 | 0.15 | 6 | 1000 | 1.19 | |
| 1864 | 37413 | T3.25 | Mini Bayonet | 1500 | 37.7 | 0.17 | 28 | 1000 | 1.19 | |
| 1893 | 37505 | T3.25 | Mini Bayonet | 2500 | 25.13 | 0.33 | 14 | 1000 | 1.19 | |
| 1895 | 37531 | G4.5 | Mini Bayonet | 2000 | 25.13 | 0.27 | 14 | 1000 | 1.06 | |
| 194 | 34761 | T3.25 | W2.1x9.2D | 2500 | 25.13 | 0.27 | 14 | 1000 | 1.054 | |
| 1992 ERD | 30215 | T3.25 | Wedge | 150 | 804 | 2.5 | 14 | 24 | 1 | |
| 214-2 BU | 34942 | T3 | End Caps | 1000 | 50.27 | 0.52 | 14 | 1000 | 1.72 | |
| 2187 | 37747 | T1.75 | 5/8" Wire Term | 7000 | 3.7 | 0.04 | 28 | 1000 | 0.52 | |
| 222 | 34967 | TL3 | Mini Screw | 5 | | 0.22 | 2 | 1000 | 0.94 | |
| 2342 24:30V30MA | 39307 | T5 | W2x4.6D | 1000 | | 0.3 | 24 | 200 | 0.78 | |
| 24E | 33181 | T2 | Slide Base # 3 | 7000 | | 0.035 | 24 | 1000 | 1.69 | |
| 24ESB | 33189 | T2 | Slide Base # 5 | 8000 | | 0.04 | 24 | 1000 | 1.11 | |
| 24MB | 33213 | T2.5 | Mini Bayonet | 10000 | 6.28 | 0.07 | 24 | 1000 | 1.19 | |
| 24PSB | 33229 | T2 | Slide Base # 5 | 10000 | | 0.072 | 24 | 1000 | 1.11 | |
| 24X | 33257 | T2 | Slide Base # 3 | 8000 | | 0.035 | 24 | 1000 | 1.69 | |
| 259 | 35027 | T3.25 | W2.1x9.2D | 5000 | 8.17 | 0.25 | 6 | 1000 | 1.054 | |
| 28ESB | 33285 | T2 | Slide Base # 5 | 6000 | | 0.04 | 28 | 1000 | 1.11 | |
| 28MB | 33311 | T2.5 | Mini Bayonet | 5000 | 3.64 | 0.04 | 28 | 1000 | 1.19 | |
| 28PSB | 33327 | T2 | Slide Base # 5 | 5000 | | 0.04 | 28 | 1000 | 1.11 | |
| 30099 PLH | 32169 | T2 | Socket | | | | | 100 | 0.91 | 2,3,4 |
| 30110 PILOT TPLR | 32161 | T2 | Dome Trans | | | | | 1000 | 0.38 | 5 |
| 30112 PILOT TPLG | 32159 | T2 | Dome Trans | | | | | 1000 | 0.38 | 5 |
| 30120 PILOT FLR | 32119 | T2 | Dome Fluted | | | | | 1000 | 0.38 | 5 |
| 31099 PLH BAY | 32173 | T2.5 & T3.25 | Socket | | | | | 100 | 1.68 | 2,4,6 |
| 313 | 35133 | T3.25 | Mini Bayonet | 500 | 43.92 | 0.17 | 28 | 1000 | 1.06 | |
| 3157WL | 59894 | S8 | Wedge | 1200 5000 | 402.12 37.69 | 2.1 0.59 | 13 14 | 1000 | 1.7 | |
| 327 | 35155 | T1.75 | SC Midg Flanged | 4000 | 4.27 | 0.04 | 28 | 1000 | 0.63 | |
| 328 | 35169 | T1.75 | SC Midg Flanged | 1000 | 4.27 | 0.2 | 6 | 1000 | 0.63 | |