



SKU: S1920  
Manufacturer: Satco  
Name: 100Q/F/DC

#### Specs

Energy Used:	100 Watts
Volts:	120 Volts
Type:	Tube T4 JD-Type
Base:	Bayonet - Double Contact Bayonet BA15d
CRI:	
Length:	2.40625 in
Diameter:	
Light Output:	1440 lumens
Average Lifetime:	2000 hours
Color:	Frosted
Beam Angle:	
Filament:	CC-8
Number in Case:	12