



PAR Reflectors

PAR30LN/PAR38



Whiter light, brighter colors, precise beam control



PAR30LN

PAR38

SATCO PAR HALOGEN LAMPS

QUALITY • VALUE • PERFORMANCE

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	CBCP	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ch.
50	PAR30/LN	Med.	S2213	50PAR30/HAL/NFL	NFL 34°	120V	2500	1750	560	CC-8	4 1/2"	Box	15
50	PAR30/LN	Med.	S2313	50PAR30/HAL/NFL	NFL 34°	130V	2500	1750	560	CC-8	4 1/2"	Box	15
50	PAR30/LN	Med.	S2214	50PAR30/HAL/WFL	WFL 50°	120V	2500	460	560	CC-8	4 1/2"	Box	15
50	PAR30/LN	Med.	S2314	50PAR30/HAL/WFL	WFL 50°	130V	2500	460	560	CC-8	4 1/2"	Box	15
50	PAR30/LN	Med.	S2215	50PAR30/HAL/NSP	NSP 9°	120V	2500	7600	550	CC-8	4 1/2"	Box	15
50	PAR30/LN	Med.	S2315	50PAR30/HAL/NSP	NSP 9°	130V	2500	7600	550	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	S2216	75PAR30/HAL/NFL	NFL 34°	120V	2500	3100	945	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	S2316	75PAR30/HAL/NFL	NFL 34°	130V	2500	3100	945	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	S2217	75PAR30/HAL/WFL	WFL 50°	120V	2500	770	945	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	S2317	75PAR30/HAL/WFL	WFL 50°	130V	2500	770	945	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	S2218	75PAR30/HAL/NSP	NSP 9°	120V	2500	13000	945	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	S2318	75PAR30/HAL/NSP	NSP 9°	130V	2500	13000	945	CC-8	4 1/2"	Box	15
45	PAR38	Med.	S2219	45PAR38/HAL/FL	FL 30°	120V	2500	1380	465	CC-8	5 5/16"	Box	15
45	PAR38	Med.	S2319	45PAR38/HAL/FL	FL 30°	130V	2500	1380	465	CC-8	5 5/16"	Box	15
45	PAR38	Med.	S2220	45PAR38/HAL/NSP	NSP 9°	120V	2500	5000	465	CC-8	5 5/16"	Box	15
45	PAR38	Med.	S2320	45PAR38/HAL/NSP	NSP 9°	130V	2500	5000	465	CC-8	5 5/16"	Box	15
75	PAR38	Med.	S2221	75PAR38/HAL/FL	FL 30°	120V	2500	3200	960	CC-8	5 5/16"	Box	15
75	PAR38	Med.	S2321	75PAR38/HAL/FL	FL 30°	130V	2500	3200	960	CC-8	5 5/16"	Box	15
75	PAR38	Med.	S2222	75PAR38/HAL/NSP	NSP 9°	120V	2500	16000	960	CC-8	5 5/16"	Box	15
75	PAR38	Med.	S2322	75PAR38/HAL/NSP	NSP 9°	130V	2500	16000	960	CC-8	5 5/16"	Box	15
90	PAR38	Med.	S2223	90PAR38/HAL/FL	FL 30°	120V	2500	3800	1260	CC-8	5 5/16"	Box	15
90	PAR38	Med.	S2323	90PAR38/HAL/FL	FL 30°	130V	2500	3800	1260	CC-8	5 5/16"	Box	15
90	PAR38	Med.	S2224	90PAR38/HAL/NSP	NSP 9°	120V	2500	14000	1260	CC-8	5 5/16"	Box	15
90	PAR38	Med.	S2324	90PAR38/HAL/NSP	NSP 9°	130V	2500	14000	1260	CC-8	5 5/16"	Box	15
120	PAR38	Med.	S2225	120PAR38/HAL/FL	FL 30°	120V	2500	4700	1600	CC-8	5 5/16"	Box	15
120	PAR38	Med.	S2325	120PAR38/HAL/FL	FL 30°	130V	2500	4700	1600	CC-8	5 5/16"	Box	15
120	PAR38	Med.	S2226	120PAR38/HAL/NSP	NSP 9°	120V	2500	22000	1600	CC-8	5 5/16"	Box	15
120	PAR38	Med.	S2326	120PAR38/HAL/NSP	NSP 9°	130V	2500	22000	1600	CC-8	5 5/16"	Box	15

halogen reflectors